# Product data sheet

Specifications





() Discontinued

## servo motor BCH, Lexium 28, 130mm, 850W, without oil seal, smooth, straight connection

BCH2MM0810CA6C

Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

### Complementary

oompicinentary	
Maximum Mechanical Speed	3000 rpm
[Us] Rated Supply Voltage	220 V
Phase	Three phase Single phase
Continuous Stall Current	5.62 A
Continuous Stall Torque	47.71 lbf.in (5.39 N.m) LXM28 7 A, 220 V, single phase 47.71 lbf.in (5.39 N.m) LXM28 7 A, 220 V, three phase
Continuous Power	850 W
Peak Stall Torque	122.14 lbf.in (13.8 N.m) LXM28 7 A, 220 V, single phase 122.14 lbf.in (13.8 N.m) LXM28 7 A, 220 V, three phase
Nominal Output Power	850 W LXM28 7 A, 220 V, single phase 850 W LXM28 7 A, 220 V, three phase
Nominal Torque	47.71 lbf.in (5.39 N.m) LXM28 7 A, 220 V, single phase 47.71 lbf.in (5.39 N.m) LXM28 7 A, 220 V, three phase
Nominal Speed	1500 rpm LXM28 7 A, 220 V, single phase 1500 rpm LXM28 7 A, 220 V, three phase
Maximum Current Irms	14.96 A LXM28 0.85 kW, 220 V
Maximum Permanent Current	6.29 A
Product Compatibility	LXM28 servo drive 0.85 kW, 220 V, single phase LXM28 servo drive 0.85 kW, 220 V, three phase
Shaft End	Smooth shaft
Shaft Diameter	0.87 in (22 mm)
Shaft Length	2.17 in (55 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	Without
Mounting Support	Asian standard flange
Motor Flange Size	5.12 in (130 mm)
Electrical Connection	Connector MIL

Disclaimer: This documen

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Torque Constant	0.96 N.m/A 68 °F (20 °C)
Back Emf Constant	58 V/krpm 68 °F (20 °C)
Rotor Inertia	13.5 kg.cm <sup>2</sup>
Stator Resistance	0.34 Ohm 68 °F (20 °C)
Stator Inductance	4.5 mH 68 °F (20 °C)
Stator Electrical Time Constant	13.24 ms 68 °F (20 °C)
Maximum Radial Force Fr	670 N 1500 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	19.7 W
Type Of Cooling	Natural convection
Length	7.36 in (187 mm)
Number Of Motor Stacks	4
Centring Collar Diameter	4.33 in (110 mm)
Centring Collar Depth	0.31 in (8 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.36 in (9.2 mm)
Circle Diameter Of The Mounting Holes	5.71 in (145 mm)
Distance Shaft Shoulder-Flange	0.31 in (8 mm)
Net Weight	21.16 lb(US) (9.6 kg)

### Environment

Ip Degree Of Protection	IP54 IM B5, IM V1 IP50 IM V3
Ambient Air Temperature For Operation	-4104 °F (-2040 °C)

## Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480733888
Returnability	No
Country Of Origin	CN

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.13 in (18.1 cm)
Package 1 Width	9.06 in (23.0 cm)
Package 1 Length	14.17 in (36.0 cm)
Package 1 Weight	21.98 lb(US) (9.97 kg)

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
 Mercury Free
 Rohs Exemption Information Yes

### **Certifications & Standards**


Reach Regulation	REACh Declaration Pro-active compliance (Product out of EU RoHS legal scope)	
Eu Rohs Directive		
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

## Product data sheet

### **Dimensions Drawings**

#### Dimensions

#### **Dimensions of Motor**




	mm	in.
L (without holding brake)	187	7.36
L (with holding brake)	216	8.5
Z	134.5	5.30

## Product data sheet BCH2MM0810CA6C

#### Performance Curves

#### Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage



Servo Motor with LXM28AU10 ... Servo Drive

- 1: Peak torque
- 2: Continuous torque