





Circuit breaker, PowerPacT B, 35A, 3 pole, 600Y/347VAC, 14kA, I-Line, thermal magnetic, 80%, ABC

BDA36035

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,012.00 USD

#### Main

Range	PowerPact
Product Name	PowerPact B
Device Short Name	BD 035
Product Or Component Type	Circuit breaker
Device Application	Distribution

### Complementary

Line Rated Current	35 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	D
Breaking Capacity	25 kA 208Y/120 V AC 50/60 Hz UL 489 25 kA 240 V AC 50/60 Hz UL 489 18 kA 480/277 V AC 50/60 Hz UL 489 18 kA 480 V AC 50/60 Hz UL 489 14 kA 600Y/347 V AC 50/60 Hz UL 489 10 kA 250 V DC UL 489
[Ue] Rated Operational Voltage	525 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	25 kA 220240 V AC 50/60 Hz IEC 60947-2 14 kA 500525 V AC 50/60 Hz IEC 60947-2 18 kA 380415 V AC 50/60 Hz IEC 60947-2 18 kA 440 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Thermal-magnetic
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	800 V IEC 60947-2
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Mechanical Durability	20000 cycles IEC 947-1 Annex K ed 5.2
Electrical Durability	10000 cycles IEC 947-1 Annex K ed 5.2 440 V In
Connection Pitch	1.06 in (27 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Awg Gauge	AWG 14AWG 2/0 aluminium/copper	
Local Signalling	Presence of auxiliary contacts flag green)	
Mounting Mode	I-Line	
Electrical Connection	I-Line connection, line Lugs, load	
Mounting Height	4.49 in (114 mm)	
Tightening Torque	31.8638.94 lbf.in (3.64.4 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 10) 44.2554.87 lbf.in (56.2 N.m) 0.020.11 in² (1070 mm²) (AWG 8AWG 2/0)	
Number Of Slots	1 auxiliary switch OF plug-in) 1 voltage release MN or MX plug-in) 1 alarm switch SD plug-in)	
Power Wire Stripping Length	0.79 in (20 mm)	
Color	Gray RAL 7016)	
9 Mm Pitches	9	
Height	5.39 in (137 mm)	
Width	3.19 in (81 mm)	
Depth	3.50 in (89 mm)	
Net Weight	2.90 lb(US) (1.315 kg)	
Quantity Per Set	Set of 1	
Phase Connection	ABC	
Circuit Breaker Application	HACR rated	

### **Environment**

UL 489 EN/IEC 60947-5-1 EN/IEC 60947-2 NEMA AB1 CSA C22.2 No 5
EN/IEC 60947-2 NEMA AB1 CSA C22.2 No 5
NEMA AB1 CSA C22.2 No 5
CSA C22.2 No 5
NMX J-266
GB 14048.2
UL
IEC
CCC
EAC
CSA
NOM
Front cover IP40 IEC 60529
IK07 conforming to IEC 62262
3 IEC 60947-1
-13158 °F (-2570 °C)
-58185 °F (-5085 °C)
< 6561.68 ft (2000 m) without derating 5000 m with derating

# Ordering and shipping details

Category	US10DE201133
Discount Schedule	0DE2
Gtin	785901051244

Returnability	Yes	
Country Of Origin	MX	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	12.80 in (32.5 cm)
Package 1 Weight	4.12 lb(US) (1.87 kg)

### Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
	Halogen Free Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov	

Apr 25, 2024