Product data sheet

Specification





Automatic switch, PowerPacT B, 125A, 2 pole, 600VAC, 18kA, EverLink lug, magnetic

BGL26000S12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 895.00 USD

Main

PowerPact	
PowerPact B	
Automatic switch	
Distribution	

Complementary

oompromontary		
Line Rated Current	125 A	
Number Of Poles	2P	
Control Type	Toggle	
Breaking Capacity Code	G	
Short-Circuit Withstand	65 kA 208Y/120 V UL 489 65 kA 240 V UL 489 35 kA 480Y/277 V UL 489 35 kA 480 V UL 489 18 kA 600 V UL 489	
[Ue] Rated Operational Voltage	600Y/347 V AC 50/60 Hz UL 489	
Magnetic Hold Current	880 A	
Magnetic Tripping Current	1320 A	
lechanical Durability 15000 cycles IEC 947-1 Annex K ed 5.2		
Electrical Durability 10000 cycles IEC 947-1 Annex K ed 5.2 440 V In		
Contact Position Indicator	Yes	
Connection Pitch	1.06 in (27 mm)	
Local Signalling	for presence of auxiliary contacts flag (green)	
Mounting Mode	Clip-on 35 x 15 mm symmetrical DIN rail) By screws plate)	
Electrical Connection	Everlink lug, line Everlink lug, load	
Awg Gauge	AWG 6AWG 2/0 fine stranded aluminium/copper AWG 14AWG 3/0 rigid or stranded aluminium/copper	
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.02 in² (2.510 mm²) 79.66 lbf.in (9 N.m) 0.020.15 in² (1695 mm²)	
Number Of Slots	1 auxiliary switch OF plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	0.79 in (20 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Color	Gray RAL 7016)	
9 Mm Pitches	6	
Height	5.39 in (137 mm)	
Width	1.42 in (36 mm)	
Depth	3.50 in (89 mm)	
Quantity Per Set	Set of 1	

Environment

Quality Labels	CE	
Standards	UL 489	
Product Certifications	UL	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)	
Operating Altitude	6561.68 ft (2000 m) without derating 5000 m with derating	

Ordering and shipping details

Category	US10DE201131	
Discount Schedule	0DE2	
Gtin	3606486289211	
Returnability	No	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	2 08 lb/LIS) (0 043 kg)



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information Y	es
Pvc Free	
Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov