# Product data sheet

Specification





## Automatic Switch, PowerPacT B, Unit Mount, 600Y/347 V AC, 125 A, 3 Pole, EverLink

BGM36000S12

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	PowerPact	
Product Name	PowerPact B	
Product Or Component Type	Automatic switch	
Device Application	Distribution	

#### Complementary

Complementary		
Line Rated Current	125 A	
Number Of Poles	3P	
Control Type	Toggle	
Breaking Capacity Code	G	
Short-Circuit Withstand	65 kA 208Y/120 V UL 489 65 kA 240 V UL 489 35 kA 480Y/277 V UL 489 35 kA 480 V UL 489 18 kA 600 V UL 489	
[Ue] Rated Operational Voltage	600Y/347 V AC 50/60 Hz UL 489	
Magnetic Hold Current 880 A		
Magnetic Tripping Current 1320 A		
Mechanical Durability	pility 15000 cycles IEC 947-1 Annex K ed 5.2	
Electrical Durability	10000 cycles IEC 947-1 Annex K ed 5.2 440 V In	
Contact Position Indicator	ator Yes	
Connection Pitch	1.06 in (27 mm)	
Local Signalling	for presence of auxiliary contacts flag (green)	
Mounting Mode	Clip-on 35 x 15 mm symmetrical DIN rail) By screws plate)	
Electrical Connection	Everlink lug, line Everlink lug, load	
Awg Gauge	AWG 6AWG 2/0 fine stranded aluminium/copper AWG 14AWG 3/0 rigid or stranded aluminium/copper	
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.02 in² (2.510 mm²) 79.66 lbf.in (9 N.m) 0.020.15 in² (1695 mm²)	
Number Of Slots	1 auxiliary switch OF plug-in) 1 voltage release MN or MX plug-in) 1 alarm switch SD plug-in)	
Power Wire Stripping Length	0.79 in (20 mm)	
Color	Gray RAL 7016)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

9 Mm Pitches	9
Height	5.39 in (137 mm)
Width	3.19 in (81 mm)
Depth	3.50 in (89 mm)
Quantity Per Set	Set of 1

## **Environment**

Quality Labels	CE	
Standards	UL 489	
Product Certifications	UL	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)	
Operating Altitude	6561.68 ft (2000 m) without derating 5000 m with derating	

## Ordering and shipping details

Category	01131 - BG UNIT MOUNT BREAKER/SWITCH	
Discount Schedule	DE2	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.39 in (13.7 cm)
Package 1 Width	3.19 in (8.1 cm)
Package 1 Length	3.50 in (8.9 cm)
Package 1 Weight	2.92 lb(US) (1.325 kg)



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	'es
<b>Ø</b>	Pvc Free	
<b>Ø</b>	Halogen Free Product	

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov