





Automatic Switch, PowerPacT B, Unit Mount, 600 V AC, 125 A, 3 Pole, EverLink

BJL36000S12

Main

Range	PowerPact
Product Name	PowerPact B
Product Or Component Type	Automatic switch
Device Application	Distribution

Complementary

Complementary		
Line Rated Current	125 A	
Number Of Poles	3P	
Control Type	Toggle	
Breaking Capacity Code	J	
Short-Circuit Withstand	100 kA 208Y/120 V UL 489 100 kA 240 V UL 489 65 kA 480Y/277 V UL 489 65 kA 480 V UL 489 25 kA 600 V UL 489	
[Ue] Rated Operational Voltage	600Y/347 V AC 50/60 Hz UL 489	
Magnetic Hold Current	880 A	
Magnetic Tripping Current	1320 A	
Mechanical Durability	15000 cycles IEC 947-1 Annex K ed 5.2	
Electrical Durability	10000 cycles IEC 947-1 Annex K ed 5.2 440 V In	
Contact Position Indicator	Yes	
Connection Pitch	1.06 in (27 mm)	
Local Signalling	for presence of auxiliary contacts flag (green)	
Mounting Mode	Clip-on 35 x 15 mm symmetrical DIN rail) By screws plate)	
Electrical Connection	Everlink lug, line Everlink lug, load	
Awg Gauge	AWG 6AWG 2/0 fine stranded aluminium/copper AWG 14AWG 3/0 rigid or stranded aluminium/copper	
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.02 in² (2.510 mm²) 79.66 lbf.in (9 N.m) 0.020.15 in² (1695 mm²)	
Number Of Slots	1 auxiliary switch OF plug-in) 1 voltage release MN or MX plug-in) 1 alarm switch SD plug-in)	
Power Wire Stripping Length	0.79 in (20 mm)	
Color	Gray RAL 7016)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

9 Mm Pitches	9
Height	5.39 in (137 mm)
Width	3.19 in (81 mm)
Depth	3.50 in (89 mm)
Quantity Per Set	Set of 1

Environment

Quality Labels	CE
Standards	UL 489
Product Certifications	UL
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category	01132-BJ/BK UNIT MOUNT BREAKER/SWITCH	
Discount Schedule	DE2	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.39 in (13.7 cm)	
Package 1 Width	3.19 in (8.1 cm)	
Package 1 Length	3.50 in (8.9 cm)	
Package 1 Weight	2.92 lb(US) (1.325 kg)	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	
Ø	Halogen Free Product	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov