Product data sheet

Specifications





servo motor BMH, Lexium 32, 3.4Nm, 8000rpm, untapped shaft, without brake, IP65, IP67, 128bit encoder

BMH0703T21A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,565.00 USD

Main

Servo motor							
ВМН							
8000 rpm							
30.09 lbf.in (3.4 N.m) LXM32.D30M2 10 A, 115 V, single phase 30.09 lbf.in (3.4 N.m) LXM32.D18M2 6 A, 230 V, single phase							
77.00 lbf.in (8.7 N.m) LXM32.D30M2 10 A, 115 V, single phase 90.28 lbf.in (10.2 N.m) LXM32.D18M2 6 A, 230 V, single phase							
650 W LXM32.D30M2 10 A, 115 V, single phase 900 W LXM32.D18M2 6 A, 230 V, single phase							
27.44 lbf.in (3.1 N.m) LXM32.D30M2 10 A, 115 V, single phase 25.67 lbf.in (2.9 N.m) LXM32.D18M2 6 A, 230 V, single phase							
2000 rpm LXM32.D30M2 10 A, 115 V, single phase 3000 rpm LXM32.D18M2 6 A, 230 V, single phase							
LXM32.D30M2 115 V single phase LXM32.D18M2 230 V single phase							
Smooth shaft							
IP65 standard IP67 with IP67 kit							
131072 points/turn							
Without							
International standard flange							
Rotatable right-angled connectors							

Complementary

Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	240 V
Phase	Three phase
Continuous Stall Current	5.55 A
Continuous Power	1.68 W
Maximum Current Irms	15 A LXM32.D30M2 17.8 A LXM32.D18M2
Maximum Permanent Current	17.84 A
Second Shaft	Without second shaft end

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

0.55 in (14 mm)
1.18 in (30 mm)
Single turn SinCos Hiperface
2.76 in (70 mm)
3
0.61 N.m/A 248 °F (120 °C)
39.3 V/krpm 248 °F (120 °C)
10
1.67 kg.cm ²
1.32 Ohm 68 °F (20 °C)
4.3 mH 68 °F (20 °C)
3.3 ms 68 °F (20 °C)
730 N 1000 rpm 580 N 2000 rpm 510 N 3000 rpm 460 N 4000 rpm 430 N 5000 rpm 400 N 6000 rpm
0.2 x Fr
Natural convection
7.32 in (186 mm)
2.36 in (60 mm)
0.10 in (2.5 mm)
4
0.22 in (5.5 mm)
3.23 in (82 mm)
0.25 m (02 mm)

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485200095
Returnability	No
Country Of Origin	DE

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.33 in (11.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	4.85 lb(US) (2.2 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



a: Power supply for servo motor brake

b: Power supply for servo motor encoder

(1) Shaft end, keyed slot (optional)

Dimensions in mm

Straight Rotatable angled connectors connectors		c (without c (with		c1	c2	c3	h	h1	Ø	Ø1 for		
b1	b2	b1	b2	brake)	brake)							screws
39.5	25.5	39.5	39.5	186	225	30	20	5	5 h9	16 ⁺⁰ _ 0.13	14 k6	M5 x 17

Dimensions in in.


Straigh conneo	raight nnectors Rotatable angled connectors		angled		angled		c (with brake)	c1	c2	c3	h	h1	ø	Ø1 for screws
b1	b2	b1	b2	brake)										
1.55	1	1.55	1.55	7.32	8.85	1.18	0.78	0.19	0.20 h9	0.63 ⁺⁰ _ 0.0051	0.55 k6	M5 x 0.67		

Performance Curves

115 V Single-Phase Supply Voltage

Torque/Speed Curves


Servo motor with LXM32•D30M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

230 V Single-Phase Supply Voltage

Torque/Speed Curves



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque