Product data sheet

Specification





servo motor BMH, Lexium 32, 48Nm, 4000rpm, untapped shaft, without brake, IP65, IP67, 128bit encoder

BMH1902P21A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3,864.00 USD

Main

Product Or Component Type	Servo motor
Device Short Name	вмн
Maximum Mechanical Speed	4000 rpm
Continuous Stall Torque	331.02 lbf.in (37.4 N.m) LXM32.D72N4 24 A, 400 V, three phase 331.02 lbf.in (37.4 N.m) LXM32.D72N4 24 A, 480 V, three phase 424.84 lbf.in (48 N.m) LXM32MD85N4 32 A, 400 V, three phase 424.84 lbf.in (48 N.m) LXM32MD85N4 32 A, 480 V, three phase 424.84 lbf.in (48 N.m) LXM32MC10N4 40 A, 400 V, three phase 424.84 lbf.in (48 N.m) LXM32MC10N4 40 A, 480 V, three phase 424.84 lbf.in (48 N.m) LXM32MC10N4 40 A, 480 V, three phase
Peak Stall Torque	893.92 lbf.in (101 N.m) LXM32.D72N4 24 A, 400 V, three phase 893.92 lbf.in (101 N.m) LXM32.D72N4 24 A, 480 V, three phase 1022.26 lbf.in (115.5 N.m) LXM32MD85N4 32 A, 400 V, three phase 1022.26 lbf.in (115.5 N.m) LXM32MD85N4 32 A, 480 V, three phase 1156.79 lbf.in (130.7 N.m) LXM32MC10N4 40 A, 400 V, three phase 1156.79 lbf.in (130.7 N.m) LXM32MC10N4 40 A, 480 V, three phase
Nominal Output Power	5900 W LXM32.D72N4 24 A, 400 V, three phase 5900 W LXM32.D72N4 24 A, 480 V, three phase 6070 W LXM32MD85N4 32 A, 400 V, three phase 6070 W LXM32MD85N4 32 A, 480 V, three phase 6070 W LXM32MC10N4 40 A, 400 V, three phase 6070 W LXM32MC10N4 40 A, 480 V, three phase
Nominal Torque	197.37 lbf.in (22.3 N.m) LXM32.D72N4 24 A, 400 V, three phase 197.37 lbf.in (22.3 N.m) LXM32.D72N4 24 A, 480 V, three phase 256.67 lbf.in (29 N.m) LXM32MD85N4 32 A, 400 V, three phase 256.67 lbf.in (29 N.m) LXM32MD85N4 32 A, 480 V, three phase 256.67 lbf.in (29 N.m) LXM32MC10N4 40 A, 400 V, three phase 256.67 lbf.in (29 N.m) LXM32MC10N4 40 A, 480 V, three phase
Nominal Speed	2000 rpm LXM32MC10N4 40 A, 400 V, three phase 2000 rpm LXM32MC10N4 40 A, 480 V, three phase 2500 rpm LXM32.D72N4 24 A, 400 V, three phase 2500 rpm LXM32.D72N4 24 A, 480 V, three phase 2500 rpm LXM32MD85N4 32 A, 400 V, three phase 2000 rpm LXM32MD85N4 32 A, 480 V, three phase
Product Compatibility	LXM32.D72N4 400480 V three phase
Shaft End	Smooth shaft
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit
Speed Feedback Resolution	131072 points/turn
Holding Brake	Without
Mounting Support	International standard flange
Electrical Connection	Rotatable right-angled connectors

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Complementary

,	
Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	480 V
Phase	Three phase
Continuous Stall Current	30.8 A
Continuous Power	6.1 W
Maximum Current Irms	72 A LXM32.D72N4
Maximum Permanent Current	114 A
Second Shaft	Without second shaft end
Shaft Diameter	1.50 in (38 mm)
Shaft Length	3.15 in (80 mm)
Feedback Type	Single turn SinCos Hiperface
Motor Flange Size	7.48 in (190 mm)
Number Of Motor Stacks	2
Torque Constant	1.56 N.m/A 248 °F (120 °C)
Back Emf Constant	108.3 V/krpm 248 °F (120 °C)
Number Of Motor Poles	10
Rotor Inertia	130.1 kg.cm²
Stator Resistance	0.15 Ohm 68 °F (20 °C)
Stator Inductance	3.86 mH 68 °F (20 °C)
Stator Electrical Time Constant	25.7 ms 68 °F (20 °C)
Maximum Radial Force Fr	4200 N 1000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	9.84 in (250 mm)
Centring Collar Diameter	7.09 in (180 mm)
Centring Collar Depth	0.16 in (4 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.55 in (14 mm)
Circle Diameter Of The Mounting Holes	8.46 in (215 mm)
Net Weight	68.34 lb(US) (31 kg)

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485264141
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	11.81 in (30.0 cm)
Package 1 Width	15.75 in (40.0 cm)
Package 1 Length	31.30 in (79.5 cm)
Package 1 Weight	80.34 lb(US) (36.44 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	4
Package 2 Height	30.31 in (77.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	340.09 lb(US) (154.26 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov