



### Overview

Model Name	APC Power Saving Back-UPS Pro 1500
Includes	CD with software , USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Madagascar , Mauritius , Mayotte , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Reunion , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

Output Power Capacity	865 Watts / 1500 VA
Max Configurable Power (Watts)	865 Watts / 1500 VA
Nominal Output Voltage	120V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Output Connections	(5) NEMA 5-15R (Battery Backup) , (5) NEMA 5-15R (Surge Protection)

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	6 feet (1.83 meters)

### Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	1
Typical recharge time	8 hour(s)
Replacement Battery	APCRBC124
RBC Quantity	1

## Communications & Management

Interface Port(s)	USB
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rating	354 Joules
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: instantaneous
Data Line Protection	Cable modem / Video protection , Network line - 10/100/1000 Base-T Ethernet (RJ-45 connector)

## Physical

Maximum Height	11.85 inches (301.0 mm)
Maximum Width	4.41 inches (112.0 mm)
Maximum Depth	15.04 inches (382.0 mm)
Net Weight	26.62 lbs (12.1 kg)
Shipping Weight	29.37 lbs (13.35 kg)
Shipping Height	15.24 inches (387.0 mm)
Shipping Width	9.37 inches (238.0 mm)
Shipping Depth	19.21 inches (488.0 mm)
Master Carton Units	1.0
SCC Codes	1073130426877 9
Units per Pallet	20.0

## Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-30000 feet (0-9000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	45.000 dB

## Conformance

Approvals	FCC Part 15 Class B , NOM , TUV , UL 1778
Standard warranty	3 years repair or replace
Equipment protection policy	Lifetime : \$150000

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs