

Product data sheet

Characteristics

C2M200S

MTR MAIN RING T-SURFACE 200A 2 SPACE QO

Product availability : Stock - Normally stocked in distribution facility



Price* : 1,083.00 USD



Main

Product or component type	Meter Mains
Range of product	QO

Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Meter socket type	Ringed
Mounting	Surface
Number of spaces	0
Number of circuits	0
Mounting	Surface
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 4...250 kcmil (aluminium/copper) line side AWG 8...AWG 2/0 for 2 cable(s) (aluminium/copper) service ground
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service feed location	OH UG
Bypass type	No bypass

Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A

GTIN	00785901291770
Nbr. of units in pkg.	1
Package weight(Lbs)	27.030000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0944 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------