

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 1,143.00 USD



Main

Product or component type	Meter Mains
Range of product	QO

Complementary

Line Rated Current	200 A
Short-circuit current	10 kA
Network number of phases	1
Meter socket type	Ringed
Mounting	Surface
Number of spaces	0
Mounting	Surface
Number of circuits	0
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 4...250 kcmil aluminium/copper)line side AWG 8...AWG 2/0 2 aluminium/copper)service ground
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	100 A
Service feed location	OH UG
Bypass type	No bypass
Depth	111.00 mm (4.37 in)
Width	497.33 mm (19.58 in)
Height	463.04 mm (18.23 in)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product certifications	UL E-6294
------------------------	-----------

Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901291787
Package weight(Lbs)	12.43 kg (27.4 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: which is known to the State of California to cause Not determined harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Will be compliant – Date to be confirmed

Contractual warranty

Warranty	18 months
----------	-----------