

Straight length, I-Line Busway, 400A, 600VAC, 3 phase, 4 wire, no integral ground bus, Cu, plug in, 10ft

CP50410

(!) Discontinued on: Nov 20, 2023

Price*: 5,080.00 USD

Main

Range Of Product	I-Line
Product Or Component Type	Straight length
Application	Plua-in

Complementary

Line Rated Current	400 A
Short Circuit Rating	22 kA
Busbar Material	Copper: busbar
Integral Ground/High Short Circuit Bracing	No integral ground bus
Rated Voltage	600 V AC
Number Of Phases	3 phase
Wiring Configuration	4-wire
Length	10 ft (3.05 m)

Environment

Product Certifications	UL listed file E22182
Standards	CSA C22.2 No 27:1997 IEC 61439-2
	UL 857

Ordering and shipping details

Category	20114-CP 400A 4WIRE-INDL
Discount Schedule	PE8
Gtin	785901460046
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	140.00 lb(US) (63.503 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation

California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive
Circularity Profile	No need of specific recycling operations
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Compliant EU RoHS Declaration

REACh Declaration