



Price\*\* : 4,151.00 USD



### Main

Product or component type	Meter Mains
Range of product	QO

### Complementary

Line Rated Current	400 A
Short-circuit current	25 kA
Network number of phases	1
Meter socket type	Ringed
Mounting	Surface Semi flush field installed flange kit
Number of spaces	8
Mounting	Semi-flush with field installed flange kit Surface
Number of circuits	16
Number of Tandem Breakers	8
Hub type	A-L
Electrical connection	Studs line side Feed-thru lugs service ground
Wire Size	AWG 4...250 kcmil aluminium)service ground AWG 4...250 kcmil copper)service ground
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	200 A
Branch Breaker Rating	200 A
Service feed location	UG
Bypass type	Class 320 manual bypass
Depth	199.90 mm (7.87 in)
Width	717.55 mm (28.25 in)
Height	1092.20 mm (43.00 in)

## Environment

Product certifications	UL E-6294
------------------------	-----------

## Ordering and shipping details

Category	00022-QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901583608
Package weight(Lbs)	17.92 oz (508.023 g)
Returnability	Yes
Country of origin	MX

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: which is known to the State of California to cause Not determined harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Will be compliant – Date to be confirmed

## Contractual warranty

Warranty	18 months
----------	-----------