Product data sheet

Specifications

SQUARE D





Safety switch, general duty, fusible, 60A, 2 pole, 15hp, 240VAC, NEMA 3R, bolt on provision, neutral factory installed

D222NRB

Product availability: Stock - Normally stocked in distribution facility

Price*: 326.00 USD

Main

Single Throw Safety Switch
General duty
Residential
Fusible disconnect switch
Neutral (factory installed)
1 phase
2
60 A
240 V AC
NEMA 3R
 1.5 hp at 120 V AC 60 Hz for 1 phase motors 3 hp at 120 V AC 60 Hz for 3 phase motors 3 hp at 240 V AC 60 Hz for 1 phase motors 7.5 hp at 240 V AC 60 Hz for 3 phase motors 10 hp at 240 V AC 60 Hz for 1 phase motors 15 hp at 240 V AC 60 Hz for 3 phase motors

Complementary

Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R
Fuse Type	H, K or R
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 12AWG 3 aluminium AWG 14AWG 3 copper
Tightening Torque	35 lbf.in (3.95 N.m) 0.000.01 in ² (2.085.26 mm ²) (AWG 14AWG 10) 35 lbf.in (3.95 N.m) (AWG 14AWG 10) 45 lbf.in (5.08 N.m) 0.01 in ² (8.37 mm ²) (AWG 8) 45 lbf.in (5.08 N.m) 0.020.03 in ² (12.321.12 mm ²) (AWG 6AWG 4) 50 lbf.in (5.65 N.m) 0.04 in ² (26.67 mm ²) (AWG 3)
Depth	4.87 in (123.70 mm)
Width	7.45 in (189.23 mm)
Height	14.88 in (377.95 mm)
Net Weight	8.82 lb(US) (4 kg)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Certifications UL listed file E2875

Ordering and shipping details

Category	US1DE1A00106
Discount Schedule	DE1A
Gtin	785901460640
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.13 in (13.03 cm)
Package 1 Width	7.63 in (19.38 cm)
Package 1 Length	16.13 in (40.97 cm)
Package 1 Weight	8.36 lb(US) (3.79 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	120
Package 2 Height	45.00 in (114.3 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1022.00 lb(US) (463.571 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
 Rohs Exemption Information Yes
 Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov