





Safety switch, general duty, fusible, 60A, 3 pole, 15hp, 240VAC, NEMA 3R, bolt on provision, neutral factory installed

D322NRB

Product availability: Stock - Normally stocked in distribution facility

Price\*: 441.00 USD

### Main

| Product                   | Single Throw Safety Switch  |  |
|---------------------------|---|--|
| Duty Rating               | General duty  |  |
| Device Application        | Residential   |  |
| Disconnect Type           | Fusible disconnect switch   |  |
| Factory Installed Neutral | Neutral (factory installed)   |  |
| Phase                     | 3 phase   |  |
| Number Of Poles           | 3   |  |
| Current Rating            | 60 A  |  |
| Voltage Rating            | 240 V AC  |  |
| Enclosure Rating Nema     | NEMA 3R   |  |
| Motor Power Hp            | 1.5 hp at 120 V AC 60 Hz for 1 phase motors 3 hp at 120 V AC 60 Hz for 3 phase motors 3 hp at 240 V AC 60 Hz for 1 phase motors 7.5 hp at 240 V AC 60 Hz for 3 phase motors 10 hp at 240 V AC 60 Hz for 1 phase motors 15 hp at 240 V AC 60 Hz for 3 phase motors |  |

### Complementary

| Short Circuit Current Rating | 100 kA maximum depending on fuse H, K or R  |  |
|------------------------------|---|--|
|                              |   |  |
| Fuse Type                    | H, K or R   |  |
| Mounting Type                | Surface   |  |
| Electrical Connection        | Lugs  |  |
| Wiring Configuration         | 4-wire (3PH + G)  |  |
| Wire Size                    | AWG 12AWG 3 aluminium   |  |
|                              | AWG 14AWG 3 copper  |  |
| Tightening Torque            | 35 lbf.in (3.95 N.m) 0.000.01 in² (2.085.26 mm²) (AWG 14AWG 10)                         |  |
|                              | 35 lbf.in (3.95 N.m) (AWG 14AWG 10)   |  |
|                              | 45 lbf.in (5.08 N.m) 0.01 in² (8.37 mm²) (AWG 8)  |  |
|                              | 45 lbf.in (5.08 N.m) 0.020.03 in <sup>2</sup> (12.321.12 mm <sup>2</sup> ) (AWG 6AWG 4) |  |
|                              | 50 lbf.in (5.65 N.m) 0.04 in <sup>2</sup> (26.67 mm <sup>2</sup> ) (AWG 3)              |  |
| Depth                        | 4.87 in (123.70 mm)   |  |
| Width                        | 7.45 in (189.23 mm)   |  |
| Height                       | 14.88 in (377.95 mm)  |  |
| Net Weight                   | 9.92 lb(US) (4.5 kg)  |  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

### **Environment**

Certifications UL listed file E2875

## Ordering and shipping details

| Category          | US1DE1A00106 |  |
|-------------------|--------------|--|
| Discount Schedule | DE1A         |  |
| Gtin              | 785901461289 |  |
| Returnability     | Yes          |  |
| Country Of Origin | US           |  |

# **Packing Units**

| _                            |                             |  |
|------------------------------|-----------------------------|--|
| Unit Type Of Package 1       | PCE                         |  |
| Number Of Units In Package 1 | 1                           |  |
| Package 1 Height             | 5.20 in (13.208 cm)         |  |
| Package 1 Width              | 7.80 in (19.812 cm)         |  |
| Package 1 Length             | 16.30 in (41.402 cm)        |  |
| Package 1 Weight             | 8.54 lb(US) (3.874 kg)      |  |
| Unit Type Of Package 2       | PAL                         |  |
| Number Of Units In Package 2 | 120                         |  |
| Package 2 Height             | 46.00 in (116.84 cm)        |  |
| Package 2 Width              | 40.00 in (101.6 cm)         |  |
| Package 2 Length             | 48.00 in (121.92 cm)        |  |
| Package 2 Weight             | 1056.00 lb(US) (478.993 kg) |  |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Compliant with Exemptions   |
| China Rohs Regulation     | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.  |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |