

Product availability : Stock - Normally stocked in distribution facility



Price** : 1,202.00 USD



Main

Product	Single Throw Safety Switch
Current Rating	200 A
Certifications	UL listed file E2875
Enclosure Rating	NEMA 1
Disconnect Type	Fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R
Mounting Type	Surface
Number of Poles	3
Electrical Connection	Lugs
Duty Rating	General duty
Voltage Rating	240 V AC
Wire Size	AWG 6...250 kcmil aluminium/copper

Complementary

Width	482.60 mm (19 in)
Height	736.60 mm (29 in)
Depth	209.55 mm (8.25 in)
Tightening torque	31.07 N.m (275 lbf.in) AWG 6...250 kcmil)

Ordering and shipping details

Category	00006 - D & DU SW, NEMA1, 30-200A
Discount Schedule	DE1A
GTIN	00785901461470
Package weight(Lbs)	19.96 kg (44.01 lb(US))
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------