





Safety switch, general duty, fusible, 200A, 3 pole, 60hp, 240VAC, NEMA 1, neutral factory installed

D324N

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,202.00 USD

Main

Product	Single Throw Safety Switch
Duty Rating	General duty
Device Application	Residential
Disconnect Type	Fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number Of Poles	3
Current Rating	200 A
Voltage Rating	240 V AC
Enclosure Rating Nema	NEMA 1
Motor Power Hp	15 hp at 240 V AC 60 Hz for 1 phase motors 25 hp at 240 V AC 60 Hz for 3 phase motors 60 hp at 240 V AC 60 Hz for 3 phase motors

Complementary

Short Circuit Current Rating	100 kA maximum depending on fuse H, K or R
Fuse Type	H, K or R
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	4-wire (3PH + G)
Wire Size	AWG 6250 kcmil aluminium/copper
Tightening Torque	275 lbf.in (31.07 N.m) (AWG 6250 kcmil)
Depth	8.25 in (209.55 mm)
Width	19 in (482.60 mm)
Height	29 in (736.60 mm)
Net Weight	55.49 lb(US) (25.17 kg)

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1DE1A00006
Discount Schedule	DE1A
Gtin	785901461470
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.60 in (21.844 cm)
Package 1 Width	19.30 in (49.022 cm)
Package 1 Length	30.50 in (77.47 cm)
Package 1 Weight	43.25 lb(US) (19.618 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	15
Package 2 Height	45.30 in (115.062 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	932.00 lb(US) (422.748 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
②	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
②	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov