Product data sheet

Specification





Fuse carrier, TeSys DF, 2P, 32A, 690VAC, fuse size 10x38mm

DF102

Product availability: Stock - Normally stocked in distribution facility

Price*: 20.40 USD

Main

Range	TeSys	
Product Name	TeSys DF	
Product Or Component Type	Fuse carrier	
Device Short Name	DF10	
Product Compatibility	DF2CA fuse cartridge DF2CN fuse cartridge	
Poles Description	2P	
Fuse Size	10 x 38 mm	
Fuse Type	, aM , gG	
Control Type	Toggle padlockable	
Utilisation Category	AC-20B IEC 60947-3 DC-20B IEC 60947-3	
[Ue] Rated Operational Voltage	690 V AC 690 V DC	
[le] Rated Operational Current	32 A 400 V AC	
[Ith] Conventional Free Air Thermal Current	32 A 68 °F (20 °C)	
[Ui] Rated Insulation Voltage	690 V AC	
[Uimp] Rated Impulse Withstand Voltage	6 kV	
Overvoltage Category	III	
Short-Circuit Withstand	120 kA 400 V IEC 60947-3 120 kA 500 V IEC 60947-3	
Power Dissipation In W	3 W maximum power dissipation by fuse	

Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1 EN 45545-2: R22 HL2
Product Certifications	IEC
	UL Recognized
	CSA
	CCC
	EAC
	DNV-GL
Mounting Support	35 mm symmetrical DIN rail

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting Position	Vertical +/- 23°)	
Connections - Terminals	screw clamp terminals 1 0.000.02 in² (116 mm²)rigid screw clamp terminals 2 0.000.01 in² (16 mm²)rigid screw clamp terminals 1 0.000.02 in² (116 mm²)flexible with or without screw clamp terminals 2 0.000.01 in² (16 mm²)flexible with or without	
Tightening Torque	19.47 lbf.in (2.2 N.m) PZ2 19.47 lbf.in (2.2 N.m) flat Ø 5.5 mm	
Height	3.13 in (79.5 mm)	
Width	1.38 in (35 mm)	
Depth	2.40 in (61 mm)	
Net Weight	0.19 lb(US) (0.085 kg)	
Quantity Per Set	Set of 6	

Environment

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-40…158 °F (-40…70 °C) with derating above 20°C	
Operating Altitude	06561.68 ft (02000 m)	
Ip Degree Of Protection	IP20	
Pollution Degree	3	
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1	
Compatibility Code	DF10	

Ordering and shipping details

Category	US10CP121714	
Discount Schedule	0CP1	
Gtin	3389119407236	
Returnability	Yes	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.38 in (3.5 cm)	
Package 1 Width	2.44 in (6.2 cm)	
Package 1 Length	3.15 in (8 cm)	
Package 1 Weight	3.17 oz (90 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	6	
Package 2 Height	2.68 in (6.8 cm)	
Package 2 Width	3.35 in (8.5 cm)	
Package 2 Length	8.74 in (22.2 cm)	
Package 2 Weight	19.96 oz (566 g)	
Unit Type Of Package 3	S03	

Number Of Units In Package 3	96
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	21.30 lb(US) (9.66 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations Circularity Profile
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov