

# Product data sheet

## Characteristics

# DF2BN1200

NFC cartridge fuses, Tesys GS, cylindrical 8.5 mm x 31.5 mm, fuse type gG, 400 VAC, 12 A, without striker

Price\*\* : 7.60 USD



! Discontinued

DF2BN1200 has not been replaced. Please contact your customer care center for more information.

### Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	400 V AC
Line Rated Current	12 A 400 V
Fuse size	8.5 x 31.5 mm
Fuse type	NFC
Quantity per set	Set of 10

### Complementary

Fuse curve	GG
Net weight	0.02 lb(US) (0.01 kg)

### Ordering and shipping details

Category	22621-IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	03389110499421
Package weight(Lbs)	0.01 lb(US) (0.004 kg)
Returnability	No

### Offer Sustainability

RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

Contractual warranty

---

Warranty	18 months
----------	-----------

---