

# Product data sheet

## Characteristics

# DF2CA16

NFC cartridge fuses, Tesys GS, cylindrical 10 mm x 38 mm, fuse type aM, 500VAC, 16 A, without striker

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\*\* : 7.60 USD



### Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	500 V AC
Fuse size	10 x 38 mm
Fuse type	NFC
Quantity per set	Set of 10

### Complementary

Line Rated Current	16 A 500 V
Fuse curve	AM
Net weight	0.02 lb(US) (0.01 kg)

### Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901573401
Package weight(Lbs)	0.00 kg (0.01 lb(US))
Returnability	No
Country of origin	FR

### Offer Sustainability

RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

---

Warranty

18 months

---