

Product data sheet

Characteristics

DF2CN06

NFC cartridge fuses, Tesys GS, cylindrical 10 mm x 38 mm, fuse type gG, 500 VAC, 6 A, without striker

Product availability : Non-Stock - Not normally stocked in distribution facility

Price** : 7.60 USD



Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	500 V AC
Line Rated Current	6 A 500 V
Fuse size	10 x 38 mm
Fuse type	NFC
Quantity per set	Set of 10

Complementary

Fuse curve	GG
Net weight	0.02 lb(US) (0.01 kg)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	03389110502107
Package weight(Lbs)	0.00 kg (0.01 lb(US))
Returnability	No
Country of origin	FR

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty

18 months
