

# Product data sheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical 10mm x 38mm, fuse type gG, 400VAC, 32A, without striker, set of 10 parts

DF2CN32

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 7.60 USD

## Main

Range Of Product	TeSys fuse-disconnector
Product Or Component Type	Cartridge fuse
Device Short Name	DF2
[Ue] Rated Operational Voltage	400 V AC
Line Rated Current	32 A 400 V
Fuse Size	10 x 38 mm
Fuse Type	NFC
Quantity Per Set	Set of 10

## Complementary

Fuse Curve	GG
Net Weight	0.02 lb(US) (0.01 kg)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
Gtin	3389110499506
Returnability	No
Country Of Origin	FR

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.51 in (1.3 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	3.15 in (8.0 cm)
Package 1 Weight	0.28 oz (8.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	0.51 in (1.3 cm)
Package 2 Width	2.17 in (5.5 cm)
Package 2 Length	3.15 in (8.0 cm)
Package 2 Weight	2.82 oz (80.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	720
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	13.20 lb(US) (5.989 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

<div>✓</div>	Reach Free Of Svhc	
<div>✓</div>	Toxic Heavy Metal Free	
<div>✓</div>	Mercury Free	
<div>✓</div>	Rohs Exemption Information	Yes
<div>✓</div>	Pvc Free	
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	