





Safety switch, double throw, fusible, 60A, 600V, 3 pole, 50HP, NEMA 3R, bolt on provision

DT362RB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 3,135.00 USD

### Main

Product	Double Throw Safety Switch		
Duty Rating	Heavy duty		
Disconnect Type	Fusible disconnect		
Factory Installed Neutral	None		
Number Of Poles	3		
Current Rating	60 A		
Voltage Rating	600 V AC 600 V DC		
Enclosure Rating	sure Rating NEMA 3		
Motor Power Hp	15 hp at 480 V AC 50-60 Hz for 3 phase motors 30 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 600 V AC 50-60 Hz for 1 phase motors 50 hp at 600 V AC 50-60 Hz for 3 phase motors 30 hp at 600 V DC		

### Complementary

Short-Circuit Current	10 kA H or K 200 kA R or J	
Fuse Type	H or K	
<del></del>	R or J	
Mounting Type	Surface	
Wire Size	AWG 12AWG 2 aluminium	
	AWG 14AWG 2 copper	
Tightening Torque	35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.26 mm²) (AWG 14AWG 10)	
	40 lbf.in (4.52 N.m) 0.01 in <sup>2</sup> (8.37 mm <sup>2</sup> ) (AWG 8)	
	45 lbf.in (5.08 N.m) 0.020.03 in² (13.321.15 mm²) (AWG 6AWG 4)	
	50 lbf.in (5.65 N.m) 0.040.05 in² (26.6733.62 mm²) (AWG 3AWG 2)	
Depth	6.6 in (167.64 mm)	
Width	11.8 in (299.72 mm)	
Height	38 in (965.20 mm)	
Net Weight	46.50 lb(US) (21.09 kg)	

### **Environment**

Certifications UL Listed

### Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10DE100133	
Discount Schedule	0DE1	
Gtin	785901308591	
Returnability	Yes	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	40.00 in (101.6 cm)	
Package 1 Width	10.00 in (25.4 cm)	
Package 1 Length	12.12 in (30.797 cm)	
Package 1 Weight	45.00 lb(US) (20.412 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov