

# Product data sheet

Specifications



Cable end, Linery TR cable ends, single conductor, brown, 10mm<sup>2</sup>, medium size, 10 sets of 100

DZ5CA102

Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.72 USD

## Main

Range Of Product	Linery
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Bag
Quantity Per Set	Set of 100
Cable Cross Section	0.02 in <sup>2</sup> (10 mm <sup>2</sup> )

## Complementary

Cable End Type	Single conductor
Additional Information	For additional marker tag holder
Color	Brown
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	1
Awg Gauge	AWG 8
Bezel Size	Ø 8.4 mm
Tube Diameter	0.19 in (4.9 mm)
Length	0.87 in (22 mm)
Tube Length	0.47 in (12 mm)
Cad Overall Depth	0.87 in (22 mm)
Net Weight	0.13 lb(US) (0.057 kg)

## Environment

Ambient Air Temperature For Operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
Gtin	3389110535594

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Returnability	Yes
---------------	-----

---

Country Of Origin	MX
-------------------	----

---

## Packing Units

---

Unit Type Of Package 1	PCE
------------------------	-----

---

Number Of Units In Package 1	1
------------------------------	---

---

Package 1 Height	0.16 in (0.400 cm)
------------------	--------------------

---

Package 1 Width	0.16 in (0.400 cm)
-----------------	--------------------

---

Package 1 Length	0.55 in (1.400 cm)
------------------	--------------------

---

Package 1 Weight	0.02 oz (0.500 g)
------------------	-------------------

---

Unit Type Of Package 2	BB1
------------------------	-----

---

Number Of Units In Package 2	100
------------------------------	-----

---

Package 2 Height	2.36 in (6.000 cm)
------------------	--------------------

---

Package 2 Width	0.79 in (2.000 cm)
-----------------	--------------------

---

Package 2 Length	5.91 in (15.000 cm)
------------------	---------------------

---

Package 2 Weight	1.90 oz (54.000 g)
------------------	--------------------

---

Unit Type Of Package 3	S02
------------------------	-----

---

Number Of Units In Package 3	6000
------------------------------	------

---

Package 3 Height	5.91 in (15.000 cm)
------------------	---------------------

---

Package 3 Width	11.81 in (30.000 cm)
-----------------	----------------------

---

Package 3 Length	15.75 in (40.000 cm)
------------------	----------------------

---

Package 3 Weight	7.80 lb(US) (3.537 kg)
------------------	------------------------

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

---

✓ Toxic Heavy Metal Free

---

✓ Mercury Free

---

✓ Rohs Exemption Information Yes

---

✓ Pvc Free

---

✓ Halogen Free Plastic Parts Product

---

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

---

**Eu Rohs Directive** Compliant  
[EU RoHS Declaration](#)

---

**China Rohs Regulation** [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

---

**Weeee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

---

**Circularity Profile** No need of specific recycling operations

---