

# Product data sheet

Specifications



Cable end, Linergy TR cable ends, single conductor, brown, 10mm<sup>2</sup>, medium size, 10 sets of 100

DZ5CA102

Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.72 USD

## Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Bag
Quantity Per Set	Set of 100
Cable Cross Section	0.02 in² (10 mm²)

## Complementary

Cable End Type	Single conductor
Additional Information	For additional marker tag holder
Color	Brown
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	1
Awg Gauge	AWG 8
Bezel Size	Ø 8.4 mm
Tube Diameter	0.19 in (4.9 mm)
Length	0.87 in (22 mm)
Tube Length	0.47 in (12 mm)
Cad Overall Depth	0.87 in (22 mm)
Net Weight	0.13 lb(US) (0.057 kg)

## Environment

Ambient Air Temperature For Operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
Gtin	3389110535594

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.400 cm)
Package 1 Width	0.16 in (0.400 cm)
Package 1 Length	0.55 in (1.400 cm)
Package 1 Weight	0.02 oz (0.500 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	2.36 in (6.000 cm)
Package 2 Width	0.79 in (2.000 cm)
Package 2 Length	5.91 in (15.000 cm)
Package 2 Weight	1.90 oz (54.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	6000
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	7.80 lb(US) (3.537 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.