# Product data sheet

Specification





Cable ends, Linergy TR cable ends, single conductor, red, 1mm<sup>2</sup>, for insulated cable, medium size, 10 sets of 100

DZ5CE010D

Product availability: Stock - Normally stocked in distribution facility

Price\*: 0.27 USD

### Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	DIN 46228-4
Type Of Packing	String of bags
Quantity Per Set	10 sets of 100
Cable Cross Section	0.00 in² (1 mm²)

### **Complementary**

-	
Cable End Type	Single conductor
Additional Information	Without marker tag holder
Color	Red
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	1
Awg Gauge	AWG 18
Bezel Size	Ø 3.5 mm
Tube Diameter	0.07 in (1.7 mm)
Length	0.55 in (14 mm)
Tube Length	0.31 in (8 mm)
Net Weight	0.22 lb(US) (0.1 kg)

#### **Environment**

Product Certifications	UL
Ambient Air Temperature For Operation	-4221 °F (-20105 °C)

## Ordering and shipping details

Category	US1000I22621
Discount Schedule	0001

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	3389110211337
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.400 cm)
Package 1 Width	0.16 in (0.400 cm)
Package 1 Length	0.55 in (1.400 cm)
Package 1 Weight	0.00 oz (0.100 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	0.98 in (2.500 cm)
Package 2 Width	4.53 in (11.500 cm)
Package 2 Length	6.69 in (17.000 cm)
Package 2 Weight	3.84 oz (109.000 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	15000
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	4.06 lb(US) (1.841 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>Ø</b>	Toxic Heavy Metal Free
<b>②</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>②</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations