

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 0.18 USD



Main

Range of product	Linery
Product or component type	Cable end
Cable end size	Short
Standards	DIN 46228-4
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	0.00 in ² (1 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Red
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG gauge	AWG 18
Bezel size	Ø 3.5 mm
Tube diameter	0.07 in (1.7 mm)
Length	0.47 in (12 mm)
Tube length	0.24 in (6 mm)
Net weight	0.21 lb(US) (0.095 kg)

Environment

Product certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	03389110211351
Package weight(Lbs)	0.00 kg (0.01 lb(US))
Returnability	No
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------