



Price** : 34,261.00 USD



EE112T3HISCUNL has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Product	Non-Linear Transformer
Enclosure Code	22D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
K-Factor	K-4
Phase	3 phases
Primary Voltage	480 V delta
Power Rating	112.5 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	6 2.5 % 2+ 4-
Temperature Rise	150 °C
Winding Material	Copper

Ordering and shipping details

Category	16278-EE K RATED LVGP XFMR
Discount Schedule	PE2E
Package weight(Lbs)	800.00 lb(US) (362.874 kg)
Returnability	No

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------