

# Product data sheet

Specifications

SQUARE D



## Square D - PowerLogic Energy Meter, EXT Range 300A, 0.90\"X1.90\" ID, 3CT's

EME3032

Discontinued on: Jan 18, 2023

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range	PowerLogic
Product Name	PowerLogic ENERGY METER
Product Or Component Type	Energy meter
Device Application	Energy monitoring

### Complementary

Type Of Measurement	Energy consumption Power Peak demand power Reactive power Power factor Voltage Current
Measurement Accuracy	+/- 1 %
Measurement Voltage	300 V AC between phase and neutral 480 V AC between phases
[Us] Rated Supply Voltage	120...277 V AC - 25...10 %
Network Frequency	50 Hz 60 Hz
Line Rated Current	300 A
Display Type	Backlit LCD
Display Size	1.2 x 3.8 inch
Information Displayed	Energy consumption Power Power maximum) Reactive power Power factor Voltage Current
Local Signalling	Phase loss NC function
Number Of Outputs	1 pulse 1 alarm output
Output Voltage	24 V AC/DC@100 mA
Impulse Duration	200 ms
Number Of Pulse	2 p/kWh 4 p/kWh 10 p/kWh 1 p/kWh

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sampling Rate	1280 Hz
Provided Equipment	3 x current transformer
Ct Size	0.90 x 1.90 inch
Standards	ANSI C12.1
Product Certifications	UL UL 3111-1 CUL
Width	7.60 in (193 mm)
Depth	Meter 2.99 in (76 mm)
Height	8.31 in (211 mm)

## Environment

Isolation Voltage	320 V
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature For Operation	32...122 °F (0...50 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)

## Ordering and shipping details

Category	US10PL109779
Discount Schedule	0PL1
Gtin	785901613763
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.88 in (20.003 cm)
Package 1 Width	8.75 in (22.225 cm)
Package 1 Length	12.00 in (30.48 cm)
Package 1 Weight	6.00 lb(US) (2.722 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>