





# Circuit breaker, FA, 240V, 60A, 2 pole, 1 phase

FA22060AB

! Discontinued

### Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

## Complementary

Line Rated Current	60 A
Number Of Poles	2P
Breaking Capacity Code	A
Mounting Mode	I-Line
Magnetic Hold Current	800 A
Magnetic Tripping Current	1450 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL100FA
Phase Connection	AB
Height	6.4 in (162.56 mm)
Width	3 in (76.20 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

## **Environment**

Certifications	UL Listed
	CSA
	IEC

# Ordering and shipping details

Category	01000-FA 240V BREAKER & SWITCH		
Discount Schedule	DE2		
Gtin	00785901253037		
Returnability	No		
Country Of Origin	MX		

# **Packing Units**

<b>Unit Type Of</b>	Package 1	PCE
Office Type Of	i ackage i	FUE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1

1

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### **Certifications & Standards**

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

**EU RoHS Declaration** 

Environmental Disclosure Product Environmental Profile