





Circuit breaker, FA, 600V, 15A, 2 pole, 2 phase

FA26015AC

! Discontinued on: Jan 23, 2021

(!) Discontinued

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

•	
Line Rated Current	15 A
Number Of Poles	2P
Breaking Capacity Code	A
Mounting Mode	I-Line
Magnetic Hold Current	275 A
Magnetic Tripping Current	600 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL50FA
Phase Connection	AC
Height	6.4 in (162.56 mm)
Width	3 in (76.20 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	CSA
	UL Listed

Ordering and shipping details

Category	01010-FA/FH 600V
Discount Schedule	DE2
Gtin	785901253761
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	4.60 in (11.684 cm)
Package 1 Width	7.80 in (19.812 cm)
Package 1 Length	12.50 in (31.75 cm)
Package 1 Weight	4.33 lb(US) (1.965 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure Product Environmental Profile