





# Circuit breaker, FA, 600V, 90A, 3 pole, shunt trip

FA360901021

#### Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

### Complementary

Line Rated Current	90 A
Number Of Poles	3P
Breaking Capacity Code	A
Mounting Mode	I-Line
Magnetic Hold Current	900 A
Magnetic Tripping Current	1700 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL50FA
Phase Connection	ABC
Height	6.4 in (162.56 mm)
Width	4.5 in (114.30 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

#### **Environment**

Certifications	CSA
	UL Listed

## Ordering and shipping details

Category	01010-FA/FH 600V
Discount Schedule	DE2
Gtin	00785901112716
Returnability	No
Country Of Origin	MX

## **Packing Units**

Unit Type Of Package 1	PCF	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1 1

Package 1 Weight 6.46 lb(US) (2.93 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
	EU RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
California Proposition 65  WARNING: This product can expose you to chemicals including: DINP known to the State of California to cause cancer, and DIDP, which is known to California to cause Birth Defects or other reproductive harm. For information go to www.p65warnings.ca.gov		