Product data sheet

Specifications



Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Line Rated Current	45 A 2P
Number Of Poles	2P
Breaking Capacity Code	A
Mounting Mode	Unit mount
Magnetic Hold Current	400 A
Magnetic Tripping Current	850 A
Electrical Connection	Lugs, load Lugs, line
Terminal Identifier	AL100FA
Phase Connection	ABC
Height	6.4 in (162.56 mm)
Width	3 in (76.20 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	CSA
	UL Listed

Ordering and shipping details

Category	00903-FAL/FHL 600V
Discount Schedule	DE2
Gtin	00785901337560
Returnability	No
Country Of Origin	МХ

Packing Units

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1

Contractual warranty

Warranty

18 months

1

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
	EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	