

Product data sheet

Specifications



Hybrid cable for Stainless LXM62-SC005_16mm, 10 m

FCE307100A200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 492.15 USD

Main

Range Of Product	PacDrive 3
Product Or Component Type	Hybrid cable

Complementary

Range Compatibility	Lexium 62
Product Compatibility	LXM 62 servo drive SHS servo motor
Type Of Cable	Shielded motor cable
Connector Type	3 x plug-in 1 x RJ45
Material	Plastic
Accessory / Separate Part Destination	Holding brake Servo motor
Cable Length	32.81 ft (10 m)
Net Weight	7.48 lb(US) (3.391 kg)

Ordering and shipping details

Category	US1PC5218353
Discount Schedule	PC52
Gtin	3606481246172
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.87 in (7.3 cm)
Package 1 Width	16.89 in (42.9 cm)
Package 1 Length	16.89 in (42.9 cm)
Package 1 Weight	7.48 lb(US) (3.391 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications