



Price** : 54.00 USD



Main

Range of product	L100/300
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L100/300
Associated complete product	HL300 L100 ML100 L300 HML100 HL100 ML300 HML300
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller lever 50.80 mm (2 in) 1 in -
Type of roller	1 steel center roller 19.05 mm (0.75 in) 6.35 mm (0.25 in)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg (0.1 lb(US))

Environment

Ambient air temperature for operation	-23...85 °C (-10...185 °F)
Ambient air temperature for storage	-23...85 °C (-10...185 °F)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21519-9007 MISCELLANEOUS
----------	--------------------------

Discount Schedule	DS1
GTIN	00785901160090
Package weight(Lbs)	1.60 oz (45.359 g)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------