





Circuit breaker, FH, 600V, 30A, 2 pole, 1 phase

FH26030AB

(!) Discontinued

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

•	
Line Rated Current	30 A
Number Of Poles	2P
Breaking Capacity Code	н
Mounting Mode	I-Line
Magnetic Hold Current	275 A
Magnetic Tripping Current	600 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL50FA
Phase Connection	AB
Height	6.4 in (162.56 mm)
Width	3 in (76.20 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	UL Listed
	CSA

Ordering and shipping details

Category	01010-FA/FH 600V
Discount Schedule	DE2
Gtin	00785901254737
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1

1

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure Product Environmental Profile