

Circuit breaker, FH, 600V, 50A

FH26050CA

Discontinued on: Jul 12, 2021

! Discontinued

Main

Product Or Component Type	Circuit breaker	
Trip Unit Technology	Thermal-magnetic	

Complementary

Line Rated Current	50 A				
Number Of Poles	2P				
Breaking Capacity Code	н				
Mounting Mode	I-Line				
Magnetic Hold Current	400 A				
Magnetic Tripping Current	850 A				
Electrical Connection	Lugs, load I-Line connection, line				
Terminal Identifier	AL100FA				
Phase Connection	CA				
Height	6.4 in (162.56 mm)				
Width	3 in (76.20 mm)				
Depth	4.13 in (104.90 mm)				
Circuit Breaker Application	HACR rated				

Environment

Certifications	UL Listed
	CSA

Ordering and shipping details

Category	01010-FA/FH 600V			
Discount Schedule	DE2			
Gtin	00785901146056			
Returnability	No			
Country Of Origin	MX			

Packing Units

Unit Type Of Package 1	PCE		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1

1

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure Product Environmental Profile