





Circuit breaker, FH, 600V, 20A, 3 pole

FH36020

! Discontinued

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Line Rated Current	20 A
Number Of Poles	3P
Breaking Capacity Code	н
Mounting Mode	I-Line
Magnetic Hold Current	275 A
Magnetic Tripping Current	600 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL50FA
Phase Connection	ABC
Height	6.4 in (162.56 mm)
Width	4.5 in (114.30 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	UL Listed
	CSA

Ordering and shipping details

Category	01010-FA/FH 600V
Discount Schedule	DE2
Gtin	00785901241331
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1

1

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure Product Environmental Profile