





Circuit breaker, FH, 600V, 100A, 3 pole, shunt trip

FH361001021

! Discontinued on: Dec 23, 2020

Main

| Product Or Component Type | Circuit breaker |
|---------------------------|------------------|
| Trip Unit Technology | Thermal-magnetic |

Complementary

| Line Rated Current | 100 A |
|-----------------------------|---------------------------------------|
| Number Of Poles | 3P |
| Breaking Capacity Code | н |
| Mounting Mode | I-Line |
| Magnetic Hold Current | 900 A |
| Magnetic Tripping Current | 1700 A |
| Electrical Connection | Lugs, load I-Line connection, line |
| Terminal Identifier | AL100FA |
| Phase Connection | ABC |
| Height | 6.4 in (162.56 mm) |
| Width | 4.5 in (114.30 mm) |
| Depth | 4.13 in (104.90 mm) |
| Circuit Breaker Application | HACR rated |

Environment

| Certifications | CSA |
|----------------|-----------|
| | UL Listed |

Ordering and shipping details

| Category | 01010-FA/FH 600V |
|-------------------|------------------|
| Discount Schedule | DE2 |
| Gtin | 00785901821717 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1

1

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure Product Environmental Profile