



Circuit breaker, FH, 600V, 40A, 3 pole

FHB36040

Discontinued on: Jul 12, 2021

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

•				
Line Rated Current	40 A			
Number Of Poles	3P			
Breaking Capacity Code	н			
Mounting Mode	I-Line			
Magnetic Hold Current	400 A			
Magnetic Tripping Current	850 A			
Electrical Connection	I-Line connection, line Bolted connection, load			
Terminal Identifier	AL100FA			
Phase Connection	ABC			
Height	6.4 in (162.56 mm)			
Width	4.5 in (114.30 mm)			
Depth	4.13 in (104.90 mm)			
Circuit Breaker Application	HACR rated			

Environment

Certifications	UL Listed
	CSA

Ordering and shipping details

Category	01010-FA/FH 600V DE2	
Discount Schedule		
Gtin	00785901338833	
Returnability	No	
Country Of Origin	MX	

Packing Units

•		
Unit Type Of Package 1	PCE	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1

1

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure Product Environmental Profile