





Circuit breaker, FH, 600V, 50A

FHL26050

! Discontinued on: Jul 12, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

① Discontinued

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Joinpionicinal y	
Line Rated Current	50 A
	60 A
Number Of Poles	2P
Breaking Capacity Code	н
Mounting Mode	Unit mount
Magnetic Hold Current	800 A
	400 A
Magnetic Tripping Current	850 A
	1450 A
Electrical Connection	Lugs, load
	Lugs, line
Terminal Identifier	AL100FA
Phase Connection	ABC
Height	6.4 in (162.56 mm)
Width	3 in (76.20 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	UL Listed
	CSA

Ordering and shipping details

Category	US10DE200903
Discount Schedule	0DE2
Gtin	00785901140382
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile