Product data sheet

Specification





gearbox straight teeth GBX, Lexium, 60mm, reduction 15:1, 12arc.min, 44N.m

GBX060015K

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 539.12 USD

Main

| Range Compatibility | Lexium 62 ILM | | | | | |
|---------------------------|-------------------------|--|--|--|--|--|
| | Lexium 28 | | | | | |
| | Lexium ILA | | | | | |
| | Lexium 62 | | | | | |
| | Lexium SD3 | | | | | |
| | Lexium ILS | | | | | |
| | Lexium 52 | | | | | |
| | Lexium ILE | | | | | |
| | Lexium 32 | | | | | |
| Product Or Component Type | Planetary gearbox | | | | | |
| Gear Box Type | Straight teeth | | | | | |
| Device Short Name | GBX | | | | | |
| Product Compatibility | BMH 2.76 in (70 mm), 1 | | | | | |
| | BSH 2.17 in (55 mm), 1 | | | | | |
| | BSH 2.17 in (55 mm), 2 | | | | | |
| | BSH 2.17 in (55 mm), 3 | | | | | |
| | BSH 2.76 in (70 mm), 1 | | | | | |
| | BRS3 | | | | | |
| | ILE 2.60 in (66 mm), 1 | | | | | |
| | ILE 2.60 in (66 mm), 2 | | | | | |
| | ILA 2.24 in (57 mm), 1 | | | | | |
| | ILA 2.24 in (57 mm), 2 | | | | | |
| | ILS 2.24 in (57 mm), 1 | | | | | |
| | ILS 2.24 in (57 mm), 2 | | | | | |
| | ILS 2.24 in (57 mm), 3 | | | | | |
| | BCH2 2.36 in (60 mm), 1 | | | | | |
| | BCH2 2.36 in (60 mm), 2 | | | | | |
| | SH3 | | | | | |
| | MH3 | | | | | |
| | ILM | | | | | |
| Gearbox External Diameter | 2.36 in (60 mm) | | | | | |
| Reduction Ratio | 15:1 | | | | | |

Complementary

| J | | | | | | |
|----------------------------|-------------------------------|--|--|--|--|--|
| Maximum Torsional Backlash | 12 arc.min | | | | | |
| Torsional Rigidity | 2.5 N.m/arcmin | | | | | |
| Housing Colour | Black | | | | | |
| Housing Material | Black anodized aluminium | | | | | |
| Shaft Material | C 45 | | | | | |
| Additional Information | Lubricated for life | | | | | |
| Service Life In Hours | 30000 h 100 rpm 86 °F (30 °C) | | | | | |
| Mounting Position | Any position | | | | | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Efficiency | 94 % | | | | | | |
|--------------------------|---|--|--|--|--|--|--|
| Maximum Radial Force Fr | 340 N 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^{\circ}\text{C}$ | | | | | | |
| Maximum Axial Force Fa | 450 N 100 rpm, during 30000 hour at 30°C | | | | | | |
| Moment Of Inertia | 0.077 kg.cm² | | | | | | |
| Continuous Output Torque | 389.43 lbf.in (44 N.m) 100 rpm 86 °F (30 °C) | | | | | | |
| Maximum Output Torque | 619.55 lbf.in (70 N.m) 100 rpm 86 °F (30 °C) | | | | | | |
| Net Weight | 2.43 lb(US) (1.1 kg) | | | | | | |
| Input Diameter | 0.55 in (14.0 mm) | | | | | | |

Environment

| Noise Level | 58 dB 1 m, no-load | | | | |
|-------------------------|----------------------|--|--|--|--|
| Ip Degree Of Protection | Shaft output IP54 | | | | |
| Ambient Temperature For | -13194 °F (-2590 °C) | | | | |

Ordering and shipping details

| Category | US1PC5318283 |
|-------------------|---------------|
| Discount Schedule | PC53 |
| Gtin | 3606480388248 |
| Returnability | No |
| Country Of Origin | DE |

Packing Units

| Unit Type Of Package 1 | PCE | | | | | |
|------------------------------|------------------------|--|--|--|--|--|
| Number Of Units In Package 1 | 1 | | | | | |
| Package 1 Height | 2.76 in (7.0 cm) | | | | | |
| Package 1 Width | 2.76 in (7.0 cm) | | | | | |
| Package 1 Length | 5.51 in (14.0 cm) | | | | | |
| Package 1 Weight | 2.22 lb(US) (1.005 kg) | | | | | |
| Unit Type Of Package 2 | S02 | | | | | |
| Number Of Units In Package 2 | 10 | | | | | |
| Package 2 Height | 5.91 in (15.0 cm) | | | | | |
| Package 2 Width | 11.81 in (30.0 cm) | | | | | |
| Package 2 Length | 15.75 in (40.0 cm) | | | | | |
| Package 2 Weight | 23.15 lb(US) (10.5 kg) | | | | | |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance




Certifications & Standards

| Reach Regulation | REACh Declaration | | | | | |
|---------------------------|---|--|--|--|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | | | | |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. | | | | | |
| Environmental Disclosure | Product Environmental Profile | | | | | |
| Circularity Profile | No need of specific recycling operations | | | | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | | | | |

GBX060015K

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

| a2 | а3 | a4 | a5 | h | g | Ø1 | Ø2 | Ø3 | Ø4 | Ø5 |
|------|----|----|-----|----|---|----|-------|-------|--------|----|
| 67.5 | 35 | 30 | 2.5 | 16 | 5 | 60 | 40 h7 | 14 h7 | M5 x 8 | 52 |

Values in in

| values | alues III III. | | | | | | | | | |
|--------|----------------|------|------|-----|------|------|---------|---------|-----------|------|
| a2 | а3 | a4 | a5 | h | g | Ø1 | Ø2 | Ø3 | Ø4 | Ø5 |
| 2.66 | 1.38 | 1.18 | 0.10 | 063 | 0.19 | 2.36 | 1.57 h7 | 0.55 h7 | M5 x 0.31 | 2.05 |