



Price* : 1,991.00 USD



GJL36020 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Circuit breaker application	HACR rated
Module type	G-frame
Range of product	Powerpact

Complementary

Rated current	20 A
System Voltage	480 V AC 600Y/347 V AC
AWG gauge	AWG 8...AWG 1/0 aluminium AWG 14...AWG 1/0 copper
Breaking capacity	18 kA 600Y/347 V 100 kA 240 V 65 kA 480 V
Electrical connection	Lugs load Lugs line
Magnetic tripping current	600...1200 A
Mounting mode	Unit mount
Number of poles	3
Product weight	3 lb(US)
Protection type	Short-circuit Overload

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Ordering and shipping details

Category	00924 - GJL THERM-MAG AND MAG-GARD
Discount Schedule	DE2

GTIN	00785901848998
Nbr. of units in pkg.	1
Package weight(Lbs)	3
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------