
# Product data sheet

Specifications





### TeSys Deca - auxiliary contact - 1 NO + 1 NC

GK2AX50

() Discontinued on: Dec 29, 2022

#### Main

Range	TeSys
Device Short Name	GK2AX
Product Or Component Type	Auxiliary contact block
Product Compatibility	GK3EF
Range Compatibility	TeSys GK3 GK3EF circuit breaker
Mounting Location	Right side
Pole Contact Composition	1 NO + 1 NC
Quantity Per Set	Set of 10

#### Complementary

[Ui] Rated Insulation Voltage	500 V IEC 60947-1
Control Type	Manual test
[Ue] Rated Operational Voltage	500 V
[Ith] Conventional Free Air Thermal Current	6 A
Protection Type	GB2CB circuit breaker GG fuse 6 A
Rated Operational Power In Va	360 VA 48 V AC-15 20000 cycles 6 A 500 VA 110127 V AC-15 20000 cycles 4.5 A 800 VA 220240 V AC-15 20000 cycles 3.5 A 850 VA 380415 V AC-15 20000 cycles 2.2 A 700 VA 440 V AC-15 20000 cycles 1.5 A 700 VA 500 V AC-15 20000 cycles 1.5 A
Rated Operational Power In W	180 W 24 V DC-13 1000 cycles 240 W 48 V DC-13 1000 cycles 180 W 60 V DC-13 1000 cycles 140 W 110 V DC-13 1000 cycles 120 W 220 V DC-13 1000 cycles
Height	3.15 in (80 mm)
Width	0.35 in (8.8 mm)
Depth	4.13 in (105 mm)
Net Weight	0.07 lb(US) (0.031 kg)

#### Environment

Environmental Characteristic Normal environment

### Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	22641-PAN,DISCONNECT,IEC ***OBSOLETE***
Discount Schedule	I
Gtin	3389110257106
Returnability	No
Country Of Origin	FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.55 in (1.4 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	3.15 in (8.0 cm)
Package 1 Weight	1.41 oz (40.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	30
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.14 lb(US) (1.425 kg)

# **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov