# Product data sheet

Specifications





## Auxiliary contacts, TeSys GS, 1 NO, early break, front mounting, for GS2 with front/side handle

GS1AM110

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 14.70 USD

#### Main

Range Of Product	TeSys	
Device Short Name	GS1AM	
Product Or Component Type	Auxiliary contact	
Contact Application	O, I and test position signalling	
Range Compatibility	TeSys TeSys GS fuse-switch disconnector FuPact FuPacT GS fuse-switch disconnector	
Contacts Type And Composition	1 NO	
Contact Operation	Early-break	
[Ith] Conventional Free Air Thermal Current	10 A (at 104 °F (40 °C))	
[le] Rated Operational Current	6 A 120 V AC-15 3 A 240 V AC-15 1.8 A 400 V AC-15 1.5 A 480 V AC-15 2.8 A 24 V DC-13 1.4 A 48 V DC-13 0.55 A 125 V DC-13 0.27 A 250 V DC-13 0.15 A 400 V DC-13	

### Complementary

Mechanical Durability	5 Mcycles		
Electrical Durability	1 Mcycles AC-15		
Switch Rated Current	30 A		
	32 A		
	50 A		
	60 A		
	63 A		
	100 A		
	125 A		
	160 A		
	200 A		
	250 A		
	315 A		
	400 A		
	600 A		
	630 A		
	800 A		
	1250 A		
Fuse Type	NFC		
	DIN		
	BS		
	CC		
	J		

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Type Of Operating Handle	External frontal External right side External left side
Mounting Location	Front face
Net Weight	0.03 lb(US) (0.015 kg)

# Ordering and shipping details

Category	US10I1122640	
Discount Schedule	0111	
Gtin	3389110181760	
Returnability	Yes	
Country Of Origin	US	

# Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	3.54 in (9 cm)	
Package 1 Width	3.15 in (8 cm)	
Package 1 Length	0.79 in (2 cm)	
Package 1 Weight	0.46 oz (13 g)	
Unit Type Of Package 2	S01	
Number Of Units In Package 2	40	
Package 2 Height	5.91 in (15 cm)	
Package 2 Width	5.91 in (15 cm)	
Package 2 Length	15.75 in (40 cm)	
Package 2 Weight	24.94 oz (707 g)	

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov