

# pushbutton head $\emptyset$ 40 mm - key release - $\emptyset$ 22 - red

GV1K02

! Discontinued on: Sep 19, 2022



#### Main

Range	TeSys
Device Short Name	GV1K
Product Or Component Type	Stop push-hutton

## Complementary

Control Type	Red push-button latching 1.57 in (40 mm)
Locking Options Description	Key release key n° 455
Height	2.85 in (72.5 mm)
Net Weight	0.21 lb(US) (0.095 kg)
Width	1.79 in (45.5 mm)

#### **Environment**

Ip Degree Of Protection IP55

### Ordering and shipping details

Category	22366-MAN STR PROTECTORS-GV1/GV3
Discount Schedule	l11
Gtin	3389110212365
Returnability	No

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.57 in (4 cm)
Package 1 Width	4.33 in (11 cm)
Package 1 Length	6.69 in (17 cm)
Package 1 Weight	3.35 oz (95 g)

#### **Contractual warranty**

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.