Product data sheet

Specification





Linergy FT, Comb busbar, 63A, 2 tap-offs, 45mm pitch

GV2G245

Product availability: Stock - Normally stocked in distribution facility

Price*: 23.30 USD

Main

Range	Linergy
Product Name	FT
Device Short Name	GV2G
Product Or Component Type	Comb busbar
Accessory / Separate Part Category	Connection accessory
Poles Description	3P
Range Compatibility	TeSys GV2 TeSys Deca TeSys U
Number Of Tap-Offs	2
[Ith] Conventional Free Air Thermal Current	63 A
Connection Pitch	1.77 in (45 mm)

Complementary

Mounting Location	On terminal
[Ui] Rated Insulation Voltage	690 V
Length	3.50 in (89 mm)
Net Weight	0.08 lb(US) (0.036 kg)

Ordering and shipping details

Category	US10I1122367
Discount Schedule	0111
Gtin	3389110555950
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2 cm)
Package 1 Width	1.57 in (4 cm)
Package 1 Length	3.74 in (9.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight	1.31 oz (37 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	100
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.51 lb(US) (3.862 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	3200
Package 3 Height	30.31 in (77 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	288.59 lb(US) (130.9 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings

Sets of Busbars $\text{GV2G}_{\bullet \bullet \bullet}$ with Terminal Block GV1G09



Sets of Busbars GV2G245, GV2G254, GV2GR272



	I
GV2G245 (2 x 45 mm)	89
GV2G254 (2 x 54 mm)	98
GV2G272 (2 x 72 mm)	116