

Product data sheet

Characteristics

GV2G354

Linergy FT - Comb busbar - 63 A - 3 tap-offs - 54 mm pitch

Product availability : Stock - Normally stocked in distribution facility



Price* : 28.70 USD



Main

Range	Linergy
Product name	FT
Device short name	GV2G
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys - GV2 TeSys - U TeSys - D TeSys - K
Number of tap-offs	3
[I _{th}] conventional free air thermal current	63 A
Connection pitch	2.13 in (54 mm)

Complementary

Mounting location	On terminal
[U _i] rated insulation voltage	690 V
Length	6.38 in (162 mm)
Product weight	0.13 lb(US) (0.06 kg)

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901490098
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1400000000000001

Returnability	Y
Country of origin	RO

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------