

Product availability : Stock - Normally stocked in distribution facility



Price** : 842.00 USD



Main

Product	Single Throw Safety Switch
Current Rating	60 A
Certifications	UL listed file E2875
Enclosure Rating	NEMA 3R galvanized steel
Factory Installed Neutral	Neutral (factory installed)
Disconnect Type	Fusible disconnect
Short Circuit Current Rating	10 kA H or K 200 kA R, J or L
Mounting Type	Surface
Number of Poles	2
Electrical Connection	Lugs
Duty Rating	Heavy duty
Voltage Rating	250 V DC 240 V AC
Wire Size	AWG 14...AWG 3 copper AWG 12...AWG 3 aluminium

Complementary

Width	168.40 mm (6.63 in)
Height	377.95 mm (14.88 in)
Depth	123.95 mm (4.88 in)
Tightening torque	5.65 N.m (50 lbf.in) AWG 3) 5.08 N.m (45 lbf.in) AWG 6...AWG 4) 4.52 N.m (40 lbf.in) 0.01 in ² (8.367 mm ²) AWG 8) 5.65 N.m (50 lbf.in) 0.00...0.01 in ² (2.06...5.261 mm ²) AWG 14...AWG 10)

Ordering and shipping details

Category	00009 - H&HU SW,2&3P,N3R,30-200A
----------	----------------------------------

Discount Schedule	DE1
GTIN	00785901478034
Package weight(Lbs)	3.80 kg (8.38 lb(US))
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------