

H226

SWITCH FUSIBLE HD 240V 600A 2P NEMA1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 5,424.00 USD



Main

Product	Single Throw Safety Switch
Line Rated Current	600 A
Certifications	UL listed file E2875
Enclosure Rating	NEMA 1 steel
Factory Installed Neutral	None
Disconnect Type	Fusible disconnect
Short Circuit Current Rating	10 kA H or K 200 kA R, J or L
Mounting Type	Surface
Number of Poles	2
Electrical Connection	Lugs
Duty Rating	Heavy duty
System Voltage	240 V AC 250 V DC
Wire Size	AWG 3/0...500 kcmil (copper or aluminium)
Wire Size	10.13 in

Complementary

Width	27.63 in
Height	50.25 in
Tightening torque	375 lbf.in (AWG 3/0...500 kcmil)

Ordering and shipping details

Category	00053 - H&HU SW,NEMA1,400-1200A
Discount Schedule	DE1
GTIN	00785901450399
Nbr. of units in pkg.	1

Package weight(Lbs)	175
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1425 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------