





Safety switch, heavy duty, fusible, 30A, 3 wire, 3 pole, 20HP, 600V AC/DC, NEMA 4, 4X, 5, 304 stainless steel

H361DS



Discontinued on: Jun 23, 2023

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	30 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 4/4X/5 stainless steel 304	
Motor Power Hp	5 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 480 V AC 50-60 Hz for 3 phase motors 7.5 hp at 600 V AC 50-60 Hz for 3 phase motors 20 hp at 600 V AC 50-60 Hz for 3 phase motors 5 hp at 250 V DC 15 hp at 600 V DC	

Complementary

Short-Circuit Current	10 kA for H or K 200 kA for R or J	
Fuse Type	H or K R or J	
Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	3-wire (3P)	
Wire Size	AWG 12AWG 6 aluminium AWG 14AWG 6 copper	
Tightening Torque	45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) (AWG 6) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)	
Depth	5.11 in (129.79 mm)	
Width	8.67 in (220.22 mm)	
Height	14.93 in (379.22 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight 13.23 lb(US) (6 kg)

Environment

Certifications UL listed file E2875

Ordering and shipping details

Category	US10DE100010	
Discount Schedule	0DE1	
Gtin	785901023616	
Returnability	No	
Country Of Origin	IIS	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.80 in (14.732 cm)	
Package 1 Width	9.10 in (23.114 cm)	
Package 1 Length	17.50 in (44.45 cm)	
Package 1 Weight	13.74 lb(US) (6.232 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	70	
Package 2 Height	e 2 Height 45.00 in (114.3 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	961.00 lb(US) (435.902 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Approximate Dimensions

